



TSP02[®] PerfaBake[®] Bakery Oven Bags

Microperforated Oven bags



Research & Development by Terinex, the world's largest producer of Polyester Oven Bags has developed for the bakery, a new innovative microperforated, high clarity product for a wide range of pastry and bread products.

The product is PerfaBake[®] Bakery Oven Bags manufactured using our TSP02[®] FDA/EEC approved foodsafe film and available in various sizes suitable for the bakery products you produce.

PerfaBake[®] Bakery Oven Bags can be used down to -30°C, therefore may be used in the freezer or for refrigerator storage. PerfaBake[®] bags can be used in the oven to finish part-baked bakery products or to reheat up to 200°C. Also suitable for use in the microwave.

Tested by major bakeries and airlines and proven to give a better baked product compared to normal bags (with or without ventilation holes). Prevents soggy finish and allows 'freshly baked' aroma to circulate.

Part bake in-store use – hygienic and cost-effective solution

Bakeries are increasingly selling part-baked bread, croissants and pastry products for final baking in the supermarket or other sales outlets. PerfaBake[®] Bakery Oven Bags are highly suitable for this, as the bakery products remain in the same packaging through to consumer purchase. The final heating process adds that lovely, crispy fresh-baked look by browning the surface of rolls and croissants etc. Additionally the appealing aroma of baking being completed in the store increases buyer's impulse to purchase.

Bake-off products

The bags are suitable for bake-off products increasingly available in supermarkets, petrol stations, caterers and leisure outlets. As they remain in the same bag from producer to consumer, hygiene is improved as the baked products are not touched by hand until served oven fresh to the final consumer.

Print

We are able to print required logos, text and bar codes on the bags.



www.terinex.co.uk

Terinex Ltd. Hammond Road, Bedford MK41 0ND, UK
Telephone: +44 (0)1234 364411 Email: sales@terinex.co.uk



EMS 505263



FM 505265